



Standard



Microscope-mounting

Work Chambers

FEATURES

- **Standard or microscope-mounting arrangements**
- **Screened bottom to contain spent particles**
- **Drop-down front panel for larger parts**
- **Internal illumination (standard unit)**

These chambers are designed for hand held work. Using a tempered safety glass top, fluorescent internal illumination, screened bottom, and conveniently sized port holes allow for easy access.

The enameled steel can be used with either laboratory or production models and should be connected to a recommended dust collector. Microscope-mounting work chamber is for use with 10X to 40X scopes.

SPECIFICATIONS

Voltage:	110 volt, 60Hz or 220V, 50Hz (Standard unit)
Dimensions:	24”L x 15”D x 13.5”H (Standard unit) 19”L x 12”D x 9”H (Microscope-mounting)
Weight:	52 LB

Airbrasive Jet Technologies, LLC

3461 South Clinton Ave, South Plainfield, NJ 07080 ph 866.272.0540

www.airbrasive.com